



Main

Range	MasterPact
Device short name	OF
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker

Complementary

Auxiliary contacts type	Low level
Signal contacts composition	1 NO/NC
Breaking capacity	5 A AC-12 240/380 V AC 50/60 Hz 5 A AC-12 480 V AC 50/60 Hz 5 A AC-12 690 V AC 50/60 Hz 5 A DC-12 250 V DC 2.5 A DC-12 250 V DC 0.5 A DC-12 48 V DC 0.3 A DC-12 24 V DC
Minimum load	2 mA at 15 V
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	6.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	150.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes