



Main

Range	MasterPact
Product or component type	Switch disconnecter
Device application	Distribution
Switch-disconnector name	MasterPact MTZ1 08 HA
Poles description	4P
Network type	AC
Network frequency	50/60 Hz

Complementary

Control type	Push-button
Mounting mode	Fixed
Upside connection	Front
Downside connection	Front
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to EN/IEC 60947-3
[Ie] rated operational current	800 A AC 50/60 Hz 690 V
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to EN/IEC 60947-3
[Uimp] rated impulse withstand voltage	12 kV conforming to EN/IEC 60947-3
[Icw] rated short-time withstand current	20 kA during 3 s conforming to EN/IEC 60947-3 36 kA during 0.5 s conforming to EN/IEC 60947-3 36 kA during 1 s
[Icm] rated short-circuit making capacity	75 kA peak 220...690 V AC at 50/60 Hz
Utilisation category	AC-23A AC-3
Performance level	HA
Suitability for isolation	Yes conforming to EN/IEC 60947-3
Contact position indicator	Yes
Visible break	No
Mechanical durability	12500 cycles with periodic preventive maintenance conforming to EN/IEC 60947-3
Electrical durability	AC-23A: 6000 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-23A: 3000 cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-3
Connection pitch	70 mm
Height	301 mm
Width	346 mm
Depth	209 mm

Environment

Net weight	18 kg
Standards	EN/IEC 60947-3
Product certifications	IECEE CB Scheme
IP degree of protection	IP30
Pollution degree	3 conforming to EN/IEC 60947-4-1

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	41.0 cm
Package 1 Width	39.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	19.242 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------