



Main

Range	MasterPact
Device short name	OF
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker

Complementary

Auxiliary contacts type	Low level
Signal contacts composition	1 NO/NC
Mounting mode	Fixed
Breaking capacity	5 A AC-12 240/380 V AC 50/60 Hz 5 A AC-12 480 V AC 50/60 Hz 5 A AC-12 690 V AC 50/60 Hz 5 A DC-12 250 V DC 2.5 A DC-12 250 V DC 0.5 A DC-12 48 V DC 0.3 A DC-12 24 V DC
Minimum load	2 mA at 15 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	6.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	38.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins