



Main

Range	MasterPact
Device short name	OF
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit breaker

Complementary

Auxiliary contacts type	Low level
Signal contacts composition	1 NO/NC
Mounting mode	Fixed
Breaking capacity	5 A AC-12 240/380 V AC 50/60 Hz 5 A AC-12 480 V AC 50/60 Hz 5 A AC-12 690 V AC 50/60 Hz 5 A DC-12 250 V DC 2.5 A DC-12 250 V DC 0.5 A DC-12 48 V DC 0.3 A DC-12 24 V DC
Minimum load	2 mA at 15 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	6.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	38.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.