



### Main

Range	MasterPact
Device short name	SDE
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit breaker

### Complementary

Auxiliary contacts type	Low level
Signal contacts composition	1 NO/NC
Mounting mode	Fixed
Breaking capacity	3 A DC-12 24/48 V DC 0.3 A DC-12 125 V DC 0.15 A DC-12 250 V DC 3 A AC-12 24/48 V AC 50/60 Hz 3 A AC-12 240 V AC 50/60 Hz 3 A AC-12 380 V AC 50/60 Hz

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	6.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	40.0 g

### Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.