



Main

Range	MasterPact
Device short name	MCH
Product or component type	Motor mechanism
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1

Complementary

Control type	Standard
Mounting mode	Drawout
[Uc] control circuit voltage	200...250 V DC
Threshold tripping voltage	0.85...1.1 Un
Maximum power consumption in VA	180 VA
Overcurrent protection	2...3 x In 0.1 s
Maximum charging time	3 s
Maximum operating frequency	<= 3 cycles per minute
Provided contact	Limit switch contact at 240 V 10 A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	12.5 cm
Package 1 Length	18.0 cm
Package 1 Weight	843.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information