



Main

Range	MasterPact
Device short name	MCH
Product or component type	Motor mechanism
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 Masterpact MasterPact MTZ3

Complementary

Control type	Standard
[Uc] control circuit voltage	48 V AC 50/60 Hz 48...60 V DC
Threshold tripping voltage	0.85...1.1 Un
Maximum power consumption in VA	180 VA
Overcurrent protection	2...3 x In 0.1 s
Maximum charging time	4 s
Maximum operating frequency	<= 3 cycles per minute
Provided contact	Limit switch contact at 240 V 10 A

Environment

Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	13.0 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.957 kg
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.183 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information