

Main

Range	MasterPact
Device short name	SDE[RETURN]PF[RETURN]OF[RETURN]micro switch
Product or component type	Auxiliary contact block
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker




Complementary

Auxiliary contacts type	Standard
Signal contacts composition	4 NO/NC
Breaking capacity	6 A AC-12 240/380 V AC 50/60 Hz 2 A AC-12 480 V AC 50/60 Hz 0.3 A DC-12 125 V DC 0.15 A DC-12 250 V DC 3 A AC-12 690 V AC 50/60 Hz
Minimum load	100 mA at 24 V
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	8.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	102.000 g
Unit Type of Package 2	BAG
Number of Units in Package 2	8
Package 2 Height	6.000 cm
Package 2 Width	18.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	2.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	64
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	12.352 kg

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes