



Main

Range	MasterPact
Device short name	micro switch[RETURN]PF[RETURN]SDE[RETURN]OF
Product or component type	Auxiliary contact block
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker

Complementary

Auxiliary contacts type	Standard
Signal contacts composition	4 NO/NC
Breaking capacity	6 A AC-12 240/380 V AC 50/60 Hz 0.5 A DC-12 125 V DC 6 A AC-12 480 V AC 50/60 Hz 6 A AC-12 690 V AC 50/60 Hz 2.5 A DC-12 24/48 V DC 0.3 A DC-12 250 V DC
Minimum load	100 mA at 24 V
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	10.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	59.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	64
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.182 kg
Unit Type of Package 3	P12
Number of Units in Package 3	512
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	45.456 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes