



Main

Range	MasterPacT
Device short name	4 OF
Product or component type	Auxiliary contact block
Device application	Control
Range compatibility	MasterPact MasterPact MTZ2 MasterPact MasterPact MTZ3

Complementary

Auxiliary contacts type	Standard
Signal contacts composition	4 NO/NC
Mounting mode	Drawout
Breaking capacity (A)	AC-12: 10 A at 240/380 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-12: 10 A at 480 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-12: 6 A at 690 V AC 50/60 Hz conforming to EN/IEC 60947-2 DC-12: 10 A at 24/48 V DC conforming to EN/IEC 60947-2 DC-12: 10 A at 125 V DC conforming to EN/IEC 60947-2 DC-12: 3 A at 250 V DC conforming to EN/IEC 60947-2 8 A at 480 V AC 50/60 Hz conforming to UL 489 6 A at 600 V AC 50/60 Hz conforming to UL 489 6 A at 250 V DC conforming to UL 489
Minimum load	2 mA at 15 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	7.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	1.066 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.