

Main

Range	MasterPact
Device short name	EF
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker
Signal contacts composition	1 NO/NC



Complementary

Auxiliary contacts type	Standard
Auxiliary contacts operation	Connected position
Mounting mode	Drawout
[Ie] rated operational current	AC-12: 6 A at 690 V AC 50/60 Hz DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC AC-12: 6 A at 240/380 V AC 50/60 Hz AC-12: 6 A at 480 V AC 50/60 Hz
Minimum load	100 mA at 24 V
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	15.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	74.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.903 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations
Take-back	No