

Main

Range	MasterPact
Device short name	EF
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker
Signal contacts composition	1 NO/NC



Complementary

Auxiliary contacts type	Low level
Auxiliary contacts operation	Connected position
Mounting mode	Drawout
[Ie] rated operational current	DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC AC-12: 5 A at 240 V AC 50/60 Hz AC-12: 5 A at 380 V AC 50/60 Hz AC-12: 5 A at 240/380 V AC 50/60 Hz
Minimum load	2 mA at 15 V
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	15.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	75.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.941 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation

 [China RoHS Declaration](#)

RoHS exemption information

 [Yes](#)
