



## Main

Range	MasterPact
Product or component type	Ethernet interface module Accessory kit
Device application	Communication
Device mounting	Embedded Direct mounting

## Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP10/100 Mbps on RJ45
Circuit breaker mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
Maximum supply current	3 A
Power consumption in W	72 W
Height	51 mm
Width	51 mm
Depth	52.5 mm
Net weight	0.075 kg
Provided equipment	1 instruction sheet
Offer type	Spare part

## Environment

Ambient air temperature for operation	-20...70 °C
---------------------------------------	-------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.89 cm
Package 1 Width	15.24 cm
Package 1 Length	21.59 cm
Package 1 Weight	131.543 g

Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>