



Main

Range	MasterPact
Product or component type	Ethernet interface module Accessory kit
Device application	Communication
Device mounting	Embedded Direct mounting

Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP10/100 Mbps on RJ45
Mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
Maximum supply current	3 A
Power consumption in W	72 W
Height	51 mm
Width	51 mm
Depth	52.5 mm
Net weight	0.075 kg
Provided equipment	1 instruction sheet
Offer type	Spare part

Environment

Ambient air temperature for operation	-20...70 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.89 cm
Package 1 Width	15.24 cm
Package 1 Length	21.59 cm
Package 1 Weight	131.543 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information