



## Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 300 m <sup>3</sup> /h at 50 Hz Free flow rate with standard filter: 350 m <sup>3</sup> /h at 60 Hz
[Us] rated supply voltage	145...253 V
Input voltage	230 V 50/60 Hz

## Complementary

Absorbed power	36 W 50 Hz 37 W 60 Hz
[In] rated current	0.16 A 60 Hz 0.17 A 50 Hz
Noise level < at	55...56 dB
Bearing type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External : 116 mm
Cut-out dimensions	223 x 223 mm
Net weight	1.3 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Faston connector
IP degree of protection	IP54

Device composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template 1 power cord
Condition of use	Surrounding environment must be relatively clean Filter must be cleaned and replaced regularly Outside temperature must be 5 °C lower than inside temperature Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	25.5 cm
Package 1 Length	27.0 cm
Package 1 Weight	1.642 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	28.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.476 kg
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	95.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	135.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------