



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	230 V
Input Connection Type	BS1363A British
Cable length	1.8 m
Number of cables	1
Provided equipment	User manual

## Physical

Colour	White
Height	5.6 cm
Width	38.5 cm
Depth	7.3 cm
Net weight	0.72 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

## Input

Network frequency	50 Hz +/- 5 Hz
Maximum input current	13 A
Switching current capacity	13 A

## Output

Number of power socket outlets	5
Outlet standard	BS 1363 United Kingdom

## Conformance

Product certifications	CE
Equipment protection policy	Lifetime : 50000 euros

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...90 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-5...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.0000000000...4572.0000000000 m




## Surge Protection and Filtering

Response time	1 ns common mode
Common mode rejection	40 dB
Peak current	24 KAcommon mode 12 kAnormal mode
Surge energy rate	918 J

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	13 cm
Package 1 Length	40.5 cm
Package 1 Weight	0.83 kg
SCC14	10731304313851

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	Limited Lifetime (European Union countries only)
----------	--------------------------------------------------