



Main

Range	WPS
Product or component type	Switch and socket-outlet
Colour tint	Light grey
Motor M-rating AS3133	M80

Complementary

Control type	Rotary
Material	PVC (polyvinyl chloride) UV stabilised
Surface finish	Gloss
Width	101 mm
Height	203 mm
Rated current	13 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	2 gangs
Pin number	3
Device composition	Flat pin
Number of poles	3
Mounting mode	Surface mounted

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	10.3 cm
Package 1 Length	20.8 cm
Package 1 Weight	833.333 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	22 cm
Package 2 Width	30.3 cm
Package 2 Length	44 cm
Package 2 Weight	10000 g
Unit Type of Package 3	P12
Number of Units in Package 3	300
Package 3 Height	130 cm

Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	268000 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation