



### Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

### Complementary

Range compatibility	Acti 9 Acti9 Isobar B distribution board
Provided equipment	Grounding bar Neutral bar DIN rail Mounting plate
[In] rated current	250 A
Incomer device options	4P switch disconnecter 4P terminal block 3P + N RCCB 3P + N MCCB 4P contactor
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	16 ways (outgoer) 1 way (incomer) - 3P + N + E
Outgoer Pole capacity	48 x 18 mm
Length	671 mm
Width	350 mm
Depth	105 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	39.0 cm
Package 1 Length	69.0 cm
Package 1 Weight	6.243 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Height	130.0 cm
Package 2 Width	112.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	164.76 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product