



Main

Range of product	Modicon M221
Product or component type	Analogue input cartridge
Product compatibility	Modicon M221C
Analogue input number	2

Complementary

Analogue input type	Current 4...20 mA Current 0...20 mA Voltage 0...10 V
Analogue input resolution	12 bits
LSB value	2.44 mV 0...10 Vvoltage 4.88 µA 0...20 mAcurrent 3.91 µA 4...20 mAcurrent
Conversion time	20 ms
Sampling duration	10 ms
Absolute accuracy error	+/- 0.1 % of full scale at 25 °C +/- 1 % of full scale
Temperature drift	+/- 0.02 %FS/°C
Repeat accuracy	+/- 0.5 %FS
Non-linearity	+/- 0.01 %FS
Cross talk	<= 1 LSB
Type of cable	Twisted shielded pairs cable
Electrical connection	3 x 1.5 mm ² 2 screw terminal blocks with pitch 3.81 mm adjustment for inputs
Maximum cable distance between devices	Twisted shielded pairs cable: <30 m for input
Insulation	Non-insulated between analogue input and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Net weight	0.015 kg
Permissible continuous overload	13 V, analogue input type: voltage 40 mA, analogue input type: current
Input impedance	<= 250 Ohm current >= 1 MOhm voltage

Environment

Immunity to microbreaks	10 ms
-------------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.594 cm
Package 1 Width	4.692 cm
Package 1 Length	7.059 cm
Package 1 Weight	30.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	75
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.31 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2400
Package 3 Height	75 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	111 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes