



Main

Range	AvatarOn
Product or component type	Power strip
Control type	Switch
Socket number	4
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.4 A
Cable length	3 m
Colour tint	Wood

Complementary

Number of socket outlets with earth pin	4
[Ue] rated operational voltage	250 V
Number of USB connection	2
[In] rated current	13 A
Outlet standard	BS 1363
Socket additional information	Shuttered
Pilot light	ON indicator
Material	PC (polycarbonate)
Length	307.5 mm
Width	61 mm
Depth	32 mm
Type of packing	Blister
Cable cross section	0...1.25 mm ²
Height	32 mm
Net weight	0.665 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.0 cm
Package 1 Length	35.5 cm
Package 1 Weight	783.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	10.156 kg
Unit Type of Package 3	P12
Number of Units in Package 3	144
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm

Package 3 Length	120.0 cm
Package 3 Weight	133.872 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information