



Main

Range	AvatarOn
Product or component type	Power strip
Shape	Rectangular
Control type	Switch
Socket number	6
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.4 A
Cable length	3 m

Complementary

Number of socket outlets with earth pin	6
[Ue] rated operational voltage	250 V
Number of USB connection	2
[In] rated current	13 A
On/off switch present	True
Outlet standard deviation	BS 1363
Surge protection present	False
Marking	With Schneider logo USB symbol
Cover present	False
Socket additional information	Shuttered
Pilot light	ON indicator
Material	PC (polycarbonate)
Length	400.5 mm
Width	61 mm
Depth	32 mm
Type of packing	Blister
Type of cable	H05VV-F3G1.25
Cable cross section	0...1.25 mm ²
Colour	White
Surface treatment	Untreated
Surface finish	Glossy
Height	32 mm
Net weight	0.742 kg

Environment

IP degree of protection	IP20
-------------------------	------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.0 cm
Package 1 Length	46.0 cm
Package 1 Weight	884.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	11.368 kg
Unit Type of Package 3	P12
Number of Units in Package 3	144
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	148.416 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information