



Main

Range	Kavacha
Product or component type	Isolating switch
Device short name	W
Device application	Control

Complementary

[Ie] rated operational current	35 A at 440 V AC-22A
Poles description	2P
Motor Rating	M180
Width	82 mm
Height	170 mm
Depth	90 mm




Environment

IP degree of protection	IP66
Standards	IEC 60947-3
Environmental characteristic	Weatherproof

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.3 cm
Package 1 Width	9 cm
Package 1 Length	8.3 cm
Package 1 Weight	1.6 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	36.5 cm
Package 2 Width	28.5 cm
Package 2 Length	43.5 cm
Package 2 Weight	17000 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
