

# XVS14BMW

Multisound siren, Harmony XVS, prewired,  
white colour, 0...105dB, 43tones, 12...24V DC



## Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

## Complementary

Colour	White
Material	ASA (Acrylonitrile Styrene Acrylate): front ASA (Acrylonitrile Styrene Acrylate): back PC (polycarbonate): back cover
Net weight	1 kg
Marking	CE
Mounting support	Bracket
Fixing mode	3 holes Ø 9 mm
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	350 mA at 24 V 250 mA at 12 V
Electrical connection	Cable: 6.5...8.5 mm, 0.33 mm <sup>2</sup> / AWG 22 (signalling circuit) Cable: 6.5...8.5 mm, 0.52 mm <sup>2</sup> / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

## Environment

Signalling type	43 tones siren
Standards	IEC 61000-6-2 EN 55014-2 EN 55022 IEC 61000-6-3
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP53 conforming to IEC 60529
[Us] rated supply voltage	12 V DC 24 V DC
Noise level	0...105 dB (continuous or intermittent tone) at 1 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30 cm
Package 1 Width	18 cm
Package 1 Length	18.5 cm
Package 1 Weight	1.307 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9.094 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	24
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	24 cm
Package 3 Weight	33.024 kg

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Siren

### Dimensions

mm  
in.

