



Main

Range of product	Harmony
Product or component type	Head for pilot light
Product specific application	For incandescent bulb
Cap/operator or lens colour	Green

Complementary

Mechanical durability	1000000 cycles
Net weight	0.015 kg
Compatibility code	ZA2B

Environment

Standards	CSA C22.2 No 14 EN/IEC 60947-5-1
Protective treatment	TH
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to IEC 61140
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	15.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.0 cm
Package 2 Width	17.0 cm
Package 2 Length	15.0 cm
Package 2 Weight	152.0 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm

Package 3 Length	40.0 cm
Package 3 Weight	1.705 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------