





Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKD XCKP XCMD XCKT

Associated body	ZCMD39L1 ZCT21N12 ZCD27 ZCMD21L5 ZCD35 ZCMD21C12 ZCD31 ZCT21G11 ZCMD25L5 ZCMD41L2 ZCP27 ZCMD29L1 ZCD26 ZCMD21L08U78 ZCP35 ZCT27P16 ZCMD29L5 ZCP28 ZCD25 ZCD21 ZCP37 ZCMD21L08R12 ZCMD81L1 ZCMD25L1 ZCT25G11 ZCT28G11 ZCMD29C12 ZCT26N12 ZCT27G11 ZCMD41L5 ZCMD21M12 ZCD37 ZCP29M12 ZCMD21L2 ZCT21P16 ZCD29M12 ZCMD37L2 ZCT26G11 ZCP29 ZCT28N12 ZCD28 ZCMD29L2 ZCMD21L1 ZCMD25L2 ZCMD81L2 ZCT25N12 ZCP21M12 ZCP21 ZCMD39L2 ZCMD61M12 ZCMD61C12 ZCMD81L5 ZCD39 ZCT28P16 ZCD29 ZCP39 ZCP25 ZCD21M12 ZCT27N12 ZCMD37L5 ZCT25P16 ZCP31 ZCMD37L1 ZCP26 ZCT26P16 ZCMD39L5 ZCMD41L1 ZCMD69C12
Movement of operating head	Linear
Type of operator	Roller lever plunger spring return thermoplastic
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With



Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.61 cm
Package 1 Width	2.266 cm
Package 1 Length	3.723 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB2
Number of Units in Package 2	10
Package 2 Height	34 cm
Package 2 Width	188 cm
Package 2 Length	229 cm
Package 2 Weight	230 g
Unit Type of Package 3	P06
Number of Units in Package 3	2560
Package 3 Height	75 cm
Package 3 Width	40 cm
Package 3 Length	80 cm
Package 3 Weight	81 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------