

## Product data sheet

### Characteristics

# AP9604S

## Silcon Triple Chassis Protocol Converter



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Number of cables	1
Provided equipment	Rack mounting brackets User manual

### Physical

Colour	Beige
Height	5.4 cm
Width	43.2 cm
Depth	16.5 cm
Net weight	1.91 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Conformance

Standards	EN 55022 class A EN 55024 EN 55082 FCC part 15 class A
Product certifications	C-Tick[RETURN]DOC/Industry Canada[RETURN]VCCI

### Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	45.7 cm
Package 1 Length	24.8 cm
Package 1 Weight	2.405 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------