

## Product data sheet

### Characteristics

# 50282

## Mobilni generator XGR Vigilohm - 220 do 240 V AC 50/60 Hz - 2,5 ma 2,5 Hz



### Predstavitev

Serijska izdelka	Vigilohm
Kratko ime naprave	XGR
Izdelek ali sestavni del	Lociranje signalnega generatorja
Ozemljitveni sistem	IT

### Komplementarno

Type of installation to be monitored	500 V - DC (Med poli) 0...760 V - AC 45 do 400 Hz (Naprava povezana na nevtralni vodnik) 0...440 V - AC 45 do 400 Hz (Naprava povezana na fazo)
Auxiliary supply voltage	220/240 V - AC 50/60 Hz
Izhodna frekvenca	2,5 Hz
Poraba energije v VA	15 VA
Merilni tok	2,5 mA
Internal impedance	40 kOhm
Material	Plastika
Teža izdelka	0,85 kg
Višina	59 mm
Širina	108 mm
Globina	189 mm

### Embalazna enota

Tip enote v embalaži 1	PCE
Število enot v embalaži 1	1
Teža embalaže 1	1,346 kg
Višina embalaže 1	11 cm
Širina embalaže 1	12,5 cm
Dolžina embalaže 1	27,5 cm

### Trajnost ponudbe

Direktiva EU ROHS	Skladnost ni zagotovljena
OEE0	Na trgih Evropske unije je treba izdelek zavreči v skladu s posebnim postopkom zbiranja odpadkov in ga ni dovoljeno zavreči skupaj z gospodinjskimi odpadki.

### Pogodbena garancija

Garancija	18 months
-----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.