

Product data sheet

Characteristics

82479

PratiKa vtičnica z zaklepanjem - 63 A - 3P + E - 200 do 250 V AC - IP65



Predstavitev

Skupina izdelkov	PratiKa
Izdelek ali sestavni del	Blokirana vtičnica
Kratko ime naprave	PratiKa vtičnica
Vtič, kategorija vtičnice	Nizka napetost
Opis polov	3P + E
Tip omrežja	AC
Standard vtičnice	Industrijski

Komplementarno

Največji [In] nazivni tok	63 A
[Ue] Nazivna operativna napetost	200 do 250 V
Omrežna frekvenca	50/60 Hz
Tip zaščite	Zaščita z odklopnikom
Vtič, material vtičnice	Ohišje Samougasljivi inženirni polimer
Povezave - terminali	Zarobljeni vijaki
Maksimalni presek kabla	16...95 mm ²
Kabelska uvodnica	Kabelska uvodnica
Vrsta navoja	Pg 42
Teža izdelka	9,1 kg
Višina	640 mm
Širina	270 mm
Globina	215 mm
Barva	Grey (RAL 7035)
Barva napetosti	Modra

Okolje

Standardi	EN 60309-1 EN 60309-2
IP stopnja zaščite	IP65 IEC 60529
IK stopnja zaščite	IK08 EN 62262
Požarna odpornost	960 °C IEC 60695-2-11
Relativna vlažnost	50 % 40 °C 70 % 30 °C 90 % 20 °C
Temperatura okoliškega zraka za delovanje	35 °C 86400 s)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Embalažna enota

Tip enote v embalaži 1	PCE
Število enot v embalaži 1	1
Teža embalaže 1	9,1 kg
Višina embalaže 1	29 cm
Širina embalaže 1	27 cm
Dolžina embalaže 1	67 cm

Pogodbena garancija

Garancija	18 months
-----------	-----------