

Product data sheet

Characteristics

83145

Unika vtičnica z zaklepanjem - 32 A - 2P + E - 380 do 415 V AC - IP44 - stena



Predstavitev

Skupina izdelkov	PratiKa
Izdelek ali sestavni del	Blokirana vtičnica
Kratko ime naprave	Unika vtičnica
Vtič, kategorija vtičnice	Nizka napetost
Opis polov	2P + E
Tip omrežja	AC
Standard vtičnice	Industrijski

Komplementarno

Montažni način	Stensko-montirano
Največji [In] nazivni tok	32 A
[Ue] Nazivna operativna napetost	380 do 415 V
Omrežna frekvenca	50/60 Hz
Ozemljitveni čas v smeri urinega kazalca	9 h
Tip zaščite	Taliina varovalka
Tip varovalke	Cilindrični
Velikost varovalke	10,3 x 38 mm
Vtič, material vtičnice	Ohišje Samougasljivi inženirni polimer
Material kontaktov	Obojka Medenina prevlečena z nikljem
Povezave - terminali	Zarobljeni vijaki
Maksimalni presek kabla	10 mm ²
Maksimalni zunanji premer kabla	25 mm
Kabelska uvodnica	Kabelska uvodnica
Vrsta navoja	Pg 21
Teža izdelka	1,172 kg
Osnovna dimenzija	103 x 255 mm
Višina	255 mm
Širina	103 mm
Globina	151 mm
Barva	Grey (RAL 7035)
Barva napetosti	Rdeča

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Okolje

Standardi	IEC 60309-1 IEC 60309-2
IP stopnja zaščite	IP44 IEC 60529
IK stopnja zaščite	IK09 conforming to EN 62262
Požarna odpornost	750 °C IEC 60695-2-11
Relativna vlažnost	50 % 40 °C 70 % 30 °C 90 % 20 °C
Temperatura okoliškega zraka za delovanje	35 °C 86400 s) -25...40 °C

Pogodbena garancija

Garancija	18 months
-----------	-----------