

## Product data sheet

### Characteristics

# 83513

## PratiKa industrijski vtič - 32 A - 2P + E - 100 do 130 V AC - IP44



### Predstavitev

Skupina izdelkov	PratiKa
Izdelek ali sestavni del	Vtič
Kratko ime naprave	PratiKa čep
Vtič, kategorija vtičnice	Nizka napetost
Opis polov	2P + E
Tip omrežja	AC
Standard vtičnice	Industrijski

### Komplementarno

Montažni način	Stensko-montirano
Vtič, vtičnica, oblika krmilne postaje	Kotni
Največji [In] nazivni tok	32 A
[Ue] Nazivna operativna napetost	100 do 130 V
Omrežna frekvenca	50/60 Hz
Ozemljitveni čep v smeri urinega kazalca	4 h
Vtič, material vtičnice	Samougasljivi inženirni polimer
Material kontaktov	Zatiči Medenina prevlečena z nikljem
Povezave - terminali	Zarobljeni vijaki
Maksimalni presek kabla	2,5...10 mm <sup>2</sup>
Maksimalni zunanji premer kabla	11,5...21 mm
Teža izdelka	0,43 kg
Osnovna dimenzija	106 x 130 mm
Višina	130 mm
Širina	106 mm
Globina	130 mm
Barva	Grey (RAL 7035)
Barva napetosti	Rumena

### Okolje

Standardi	EN 60309-2 EN 60309-1
IP stopnja zaščite	IP44 IEC 60529
IK stopnja zaščite	IK08 EN 62262
Požarna odpornost	850 °C conforming to IEC 60695-2-1
Relativna vlažnost	50 % 40 °C 70 % 30 °C 90 % 20 °C
Nadmorska višina delovanja	2000 m
Temperatura okoliškega zraka za delovanje	35 °C 86400 s ) -25...40 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Embalažna enota

Teža embalaže 1	359 g
-----------------	-------

## Pogodbena garancija

Garancija	18 months
-----------	-----------