

Product data sheet

Characteristics

LMR9341004

Easy Styl, Modular stikalo zatemnilno LED 2M srebro



Predstavitev

Serijska izdelka	Easy Styl
Skupina izdelkov	Easy Styl
Izdelek ali sestavni del	Zatemnilnik
Predstavitev naprave	Mehanizem
Preklopna funkcija	Zatemnilnik
Združljivost serije/ obsega	Easy Styl
Število modulov	2 modula
Način pritrdjevanja	Vpet
Barvni odtenek	Črna
Tip pakiranja	Plastična vrečka z nalepko
Količina na set/komplet	1
Regulator zatemnitve	270° vrtljiva nastavitvev
[Ue] Nazivna operativna napetost	220/240 V AC 50 Hz
Tip obremenitve	Žarnica z žarilno nitko Halogenska svetilka
Material	ABS + PC
Višina	51 mm
Širina	22 mm
Globina	68 mm
Teža izdelka	0,033 kg
IK stopnja zaščite	IK01
Zdravje in problemi okolja	Brez halogena

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.