

Product data sheet
Characteristics

ZCT27G11

Ohišje omejitvenega stikala ZCT - kompaktno -
2NC - počasna prekinitev - Pg 11



Predstavitev

Serijska izdelka	OsiSense XC
Ime serije	Standardni kompaktni
Izdelek ali sestavni del	Ohišje mejnega stikala
Kratko ime naprave	ZCT
Zasnova	Compact
Tip ohišja	Fiksen
Povezana glava	ZCE05 ZCEH2 ZCE14 ZCE62 ZCE02 ZCE64 ZCE65 ZCE01 ZCE28 ZCE06 ZCE66 ZCE21 ZCE24 ZCE27 ZCE11 ZCE08 ZCEH0 ZCE13 ZCE63 ZCE29 ZCE10 ZCE67 ZCE07
Material ohišja	Plastika
Število polov	2
Tip kontakta in sestava	2 NC
Premik kontakta	Slow-break, simultaneous

Komplementarno

Električna povezava	Terminali z vijakno objemko 1 x 0,5 do 2 x 2,5 mm ²
Kabelska uvodnica	2 vrezana vhoda za kabel Pg 11 4...8 mm
Kontaktna izolacijska oblika	ZB
Material kontaktov	Posrebreni kontakti
Pozitivna odprtina	Z
Minimalna hitrost aktiviranja	6 m/s
Oznaka kontaktne kode	B300, AC-15 (U _e = 240 V), I _e = 1,5 A EN/IEC 60947-5-1 dodatek A R300, DC-13 (U _e = 250 V), I _e = 0,1 A EN/IEC 60947-5-1 dodatek A
[Ui] Nazivna izolacijska trdnost	300 VUL 508 500 V 3)IEC 60947-1 300 VCSA C22.2 št. 14
[Uimp] Nazivna napetostna trdnost ob impulzu	6 kV IEC 60664 6 kV IEC 60947-1
Kratkostična zaščita	10 A Modul Talilna varovalka gG
Električna vzdržljivost	5000000 Cycles, DC-13 120 V, 7 W 60 cyc/mn 0,5 IEC 60947-5-1 dodatek C 5000000 Cycles, DC-13 24 V, 13 W 60 cyc/mn 0,5 IEC 60947-5-1 dodatek C 5000000 cycles, DC-13 48 V, 9 W 60 cyc/mn 0,5 IEC 60947-5-1 dodatek C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Širina	58 mm
Višina	51 mm
Globina	30 mm
Teža izdelka	0,13 kg

Okolje

Združljivost izdelkov	XCKT
Temperatura okoliškega zraka za delovanje	-25...70 °C
Temperatura okoliškega zraka za skladiščenje	-40...70 °C

Trajnost ponudbe

Status trajnostne ponudbe	Izdelek Green Premium
Direktiva EU ROHS	Proaktivno zagotavljanje skladnosti (izdelek je zunaj področja uporabe direktive EU RoHS) Izjava EU RoHS
Brez živega srebra	Da
Informacije o izvzetju iz RoHS	Da
Razkritje okoljskih podatkov	Okoljski Profil Izdelka
Profil krožnega gospodarstva	Informacije O Izteku Življenjske Dobe

Pogodbena garancija

Garancija	18 months
-----------	-----------