

Product data sheet

Characteristics

LA4DWB

TeSys Deca - interface amplifier module - solid state - 24V DC/250V AC



Main

Range	TeSys
Device short name	LA4D
Poles description	3P
Product or component type	Interface module
Product compatibility	LC1D09...D115

Complementary

Mounting mode	Top mounted
Technology type	Solid state
[Us] rated supply voltage	24 V DC
Control circuit voltage limits	5...30 V at 20 °C DC
[Ui] rated insulation voltage	250 V - for control circuit conforming to IEC 60947-5-1
Connections - terminals	Control circuit: connector 1 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: connector 1 cable(s) 1...2.5 mm ² flexible without cable end Control circuit: connector 1 cable(s) 1...2.5 mm ² solid with cable end Control circuit: connector 1 cable(s) 1...2.5 mm ² solid without cable end Control circuit: connector 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: connector 2 cable(s) 1...2.5 mm ² flexible without cable end Control circuit: connector 2 cable(s) 1...2.5 mm ² solid with cable end Control circuit: connector 2 cable(s) 1...2.5 mm ² solid without cable end
[Ue] rated operational voltage	Control circuit: 24...250 V AC
Current consumption	8.5...15 mA 20 °C
Current state 0 guaranteed	<= 2 mA
Voltage state 0 guaranteed	< 2.4 V
Voltage state 1 guaranteed	5 V
Electrical durability	20 Mcycles at 240 V
Local signalling	LED indicator
Height	19 mm
Net weight	0.045 kg

Environment

Standards	IEC 60255-5
Product certifications	CSA[RETURN]UL
[Ith] conventional free air thermal current	8 A 50 °C
Protection type	Built-in by diode
IP degree of protection	IP2X conforming to IEC 60529
Ambient air temperature for operation	-25...55 °C
Permissible ambient air temperature around the device	-25...70 °C
Ambient air temperature for storage	-40...80 °C

Heat dissipation	0.4 W for control circuit
Immunity to microbreaks	1 ms

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	4.8 cm
Package 1 Length	5.0 cm
Package 1 Weight	56.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	70
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------