

Product data sheet

Characteristics

VZ11

TeSys VARIO - additional neutral block - 40 A -
for V02...V2



Main

Range	TeSys
Device short name	VZ
Product or component type	Additional neutral block
Performance level	High performance
Poles description	1N
Contacts type and composition	1 NO
Contact operation	Early make, late break
Product compatibility	V1 V2 V02 V0 V01
Range compatibility	TeSys TeSys VARIO switch disconnecter
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	40 A
Mechanical durability	100000 cycles
Electrical durability	30000 Cycles DC-1...5 100000 cycles AC-21
Connections - terminals	Screw clamp terminals6 mm ² - flexible - with cable end Screw clamp terminals10 mm ² - solid
Tightening torque	2.1 N.m - on screw clamp terminals
Height	74 mm
Width	16 mm
Depth	35 mm
Net weight	0.05 kg

Environment

Standards	IEC 60947-3
Product certifications	GL[RETURN]CSA[RETURN]UL[RETURN]UKCA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	5.5 cm
Package 1 Length	9.0 cm
Package 1 Weight	48.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	69
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.582 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------