

# Product data sheet

## Characteristics

# 1007003C

Meter socket, ringless, 3 phase, 4 wire, 20A,  
13 jaws, 600VAC max, solid top, no bypass, no  
jaw release

### Main

Product or Component Type	Meter Socket
Meter socket type	Ringless
Hub type	Solid top

### Complementary

Meter socket rated current	20 A
Number of jaws	13 without jaw release
Bypass type	No bypass
Phase	3 phase
[Ue] rated operational voltage	600 V AC
Enclosure Material	Steel
Electrical connection	Lugs slotted
Service feed location	UG
Wiring configuration	4-wire
Device mounting	Surface
AWG gauge	AWG 14...AWG 2/0 aluminium/copper)line side AWG 14...AWG 2/0 aluminium/copper)service ground

### Environment

Product Certifications	UL Listed
Enclosure Rating	NEMA 3R

### Ordering and shipping details

Category	US10DE400039
Discount Schedule	0DE4
GTIN	785901542179
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.60 in (11.684 cm)
Package 1 Width	14.80 in (37.592 cm)
Package 1 Length	17.30 in (43.942 cm)
Package 1 Weight	19.421 lb(US) (8.809 kg)

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	"WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> "
EU RoHS Directive	Under investigation
Take-back	No

## Contractual warranty

Warranty	18 months
----------	-----------