

### Main

|                       |                               |
|-----------------------|-------------------------------|
| Product               | Torroidal Current Transformer |
| Certifications        | UL Recognized                 |
| Ratio                 | 400/5                         |
| Enclosure Type        | NEMA 1                        |
| Phase                 | 1 phase                       |
| Electrical Connection | Screw clamp terminals         |
| Opening Size          | Ø 5.75 in                     |



### Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 15500-CLASS 4210 CT'S (LC 5101) |
| Discount Schedule     | PA1                             |
| GTIN                  | 785901036999                    |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 10.10 lb(US) (4.581 kg)         |
| Returnability         | No                              |
| Country of origin     | MX                              |

### Packing Units

|                        |                     |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE                 |
| Package 1 Height       | 8.94 in (22.708 cm) |
| Package 1 width        | 2.12 in (5.385 cm)  |
| Package 1 Length       | 8.50 in (21.59 cm)  |

### Offer Sustainability

|                             |   |
|-----------------------------|---|
| California proposition 65   | WARNING: This product can expose you to chemicals including: Methanol, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation            |  <a href="#">REACH Declaration</a>   |
| REACH free of SVHC          | Yes   |
| EU RoHS Directive           | Compliant  <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free      | Yes   |
| Mercury free                | Yes   |
| RoHS exemption information  |  <a href="#">Yes</a>   |
| China RoHS Regulation       |  <a href="#">China RoHS Declaration</a>  |
| PVC free                    | Yes   |
| Halogen content performance | Halogen free plastic parts product  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|