



Main

Range	Acti9
Device short name	iCH
Product or Component Type	Hour counter
Range compatibility	Prisma Prisma P door Prisma Prisma G door
Type of measurement	Operating time
Display type	Electromechanical 7 2
Maximum value measured	99999.99 h

Complementary

Full scale display	99999.99
Reset	Without
Display accuracy	0.0001
[Us] rated supply voltage	230 V AC 50 Hz
Power consumption in VA	0.15 VA
Mounting Mode	Fixed
Mounting Support	DIN rail

Environment

9 mm pitches	4
IP degree of protection	Front face: IP65
Width	1.42 in (36 mm)
Height	3.54 in (90 mm)
Depth	2.64 in (67 mm)

Ordering and shipping details





Category	US10DE201078
Discount Schedule	0DE2
GTIN	3303430154402
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.99 in (7.6 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	3.32 oz (94.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	15.74 lb(US) (7.141 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------