



### Main

Range	Acti9
Device short name	iCI
Product or Component Type	Impulse counter
Range compatibility	Prisma Prisma P door Prisma Prisma G door
Type of measurement	Impulse number
Display type	Electromechanical 7
Maximum value measured	9999999

### Complementary

Full scale display	9999999
Impulse duration	50 ms
Time between 2 impulse	50 ms
Reset	Without
[Us] rated supply voltage	230 V AC 50/60 Hz
Power consumption in VA	0.15 VA
Mounting Mode	Fixed
Mounting Support	DIN rail

### Environment

9 mm pitches	4
Width	1.42 in (36 mm)
Height	3.54 in (90 mm)
Depth	2.64 in (67 mm)

### Ordering and shipping details





Category	US10DE201078
Discount Schedule	0DE2
GTIN	3303430154433
Returnability	No
Country of origin	DE

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	2.91 in (7.4 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	3.28 oz (93.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	15.68 lb(US) (7.111 kg)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------