

2510MBW11

Manual starter, integral horsepower, NEMA M0, 600VAC, 2 pole, 2HP at 230VAC, 1 phase, no indicator, NEMA 4/4X

Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	1 Hp 115 V AC, 1 phase 2 hp 230 V AC, 1 phase
Voltage Rating	600 V AC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	10.92 in (277.37 mm)
Width	5.78 in (146.81 mm)
Depth	5.76 in (146.30 mm)

Environment

Certifications	CSA LR60905 class 3211 05[RETURN]UL listed file E42243 CCN NLRV
NEMA Enclosure Rating	NEMA 4/4X brushed stainless steel

Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1
GTIN	785901057642
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.80 in (17.272 cm)
Package 1 Width	6.00 in (15.240 cm)
Package 1 Length	11.40 in (28.956 cm)
Package 1 Weight	7.500 lb(US) (3.402 kg)

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------