

## 2510TCO3

Manual Starter, integral horsepower, NEMA M1, 600 VAC, 3 pole, 10 HP at 380/575 VAC, three phase, no indicator, open



### Main

Product	Manual Starter
Type	T
NEMA Size	M-1

### Complementary

Control Unit	Toggle switch
Pilot Light	No indicator
Horsepower Rating	7.5 Hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	5.72 in (145.29 mm)
Width	3.5 in (88.90 mm)
Depth	4.03 in (102.36 mm)

### Environment

Certifications	UL listed file E42243 CCN NLRV[RETURN]CSA LR60905 class 3211 05
NEMA Enclosure Rating	Not rated (open device)

### Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1
GTIN	785901795827
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.40 in (16.256 cm)
Package 1 Width	4.90 in (12.446 cm)
Package 1 Length	8.60 in (21.844 cm)
Package 1 Weight	34.88 oz (988.831 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------