

Main

Product	Split Core Current Transformer
Certifications	UL Recognized
Ratio	1000/5
Enclosure Type	NEMA 1
Phase	1 phase
Electrical Connection	Screw clamp terminals
Opening Size	3.56 x 8.81 in



Ordering and shipping details

Category	15500-CLASS 4210 CT'S (LC 5101)
Discount Schedule	PA1
GTIN	785901862963
Nbr. of units in pkg.	1
Package weight(Lbs)	13.00 lb(US) (5.897 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.40 in (8.636 cm)
Package 1 width	13.90 in (35.306 cm)
Package 1 Length	16.10 in (40.894 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Methanol, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------