

Product data sheet

Characteristics

2S51F

[TAA, BAA, BABA, BAA_COTS] Transformer, dry type, encapsulated, 2kVA, 1 phase, 600V primary, 120/240V secondary, 9A, 115C rise

Main

Product or Component Type	Dry Sealed Transformer
Primary to Secondary Voltage	600 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	9A
Phase	1 phase
Power Rating	2 kVA
Temperature rise	115 °C
Height	9.56 in (242.82 mm)
Width	8.68 in (220.47 mm)
Depth	6.56 in (166.62 mm)
Enclosure mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product Certifications	cULus[RETURN]UL Listed[RETURN]CSA

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
GTIN	785901020356
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.50 in (24.13 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	12.90 in (32.766 cm)
Package 1 Weight	49.500 lb(US) (22.453 kg)

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------