

# Product data sheet

## Characteristics

# 3106340938

NEMA Motor Starter, Type S, replacement coil, 110/120VAC 50/60Hz, 2 or 3 pole, NEMA Size 2 starter and 8903SP lighting



### Main

Product or Component Type	Coil
Accessory / separate part destination	Class 8502 type SD contactor[RETURN]Class 8903 type SP lighting contactor

### Complementary

NEMA size	2
[Ue] rated operational voltage	120 V AC 60 Hz 110 V AC 50 Hz
Inrush power in VA	296 VA 311 VA
Average consumption	36 VA 37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

### Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
GTIN	785901484882
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	12.80 oz (362.874 g)

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

### Contractual warranty

Warranty	18 months
----------	-----------