

Product data sheet

Characteristics

3106340947

NEMA Motor Starter, Type S, replacement coil,
220/240VAC 50/60Hz, 2 or 3 pole, NEMA Size
2 starters, 8903SP lighting



Main

Product or Component Type	Coil
Accessory / separate part destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

Complementary

NEMA size	2
[Ue] rated operational voltage	240 V AC 60 Hz 220 V AC 50 Hz
Inrush power in VA	296 VA 311 VA
Average consumption	36 VA 37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
GTIN	785901504979
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	12.96 oz (367.41 g)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------