

# Product data sheet

## Characteristics

# 3106340957

NEMA Motor Starter, Type S, replacement coil, 440/480VAC 50/60Hz, 2 or 3 pole, NEMA Size 2 starter and 8903SP lighting



### Main

|                                       |                                                                           |
|---------------------------------------|---------------------------------------------------------------------------|
| Product or Component Type             | Coil                                                                      |
| Accessory / separate part destination | Class 8502 type SD contactor[RETURN]Class 8903 type SP lighting contactor |

### Complementary

|                                |                                  |
|--------------------------------|----------------------------------|
| NEMA size                      | 2                                |
| [Ue] rated operational voltage | 480 V AC 60 Hz<br>440 V AC 50 Hz |
| Inrush power in VA             | 296 VA<br>311 VA                 |
| Average consumption            | 36 VA<br>37 VA                   |
| Height                         | 2.61 in (66.2 mm)                |
| Width                          | 3.98 in (101.1 mm)               |
| Depth                          | 2.43 in (61.7 mm)                |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP118061 |
| Discount Schedule | 0CP1         |
| GTIN              | 785901048831 |
| Returnability     | Yes          |
| Country of origin | MX           |

### Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 2.72 in (6.9 cm)       |
| Package 1 Width              | 4.02 in (10.2 cm)      |
| Package 1 Length             | 2.72 in (6.9 cm)       |
| Package 1 Weight             | 0.72 lb(US) (0.327 kg) |

### Offer Sustainability

|                   |                                            |
|-------------------|--------------------------------------------|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--------------------------------------------|

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|