

# Product data sheet

## Characteristics

# 45T3HNV

Transformer, dry type, nonventilated, 45kVA, 3 phase, 480V primary, 208Y/120V secondary, 19E, 150C rise

### Main

Product	Non-Ventilated Transformer
Enclosure Code	19E
Insulation Temperature	428 °F (220 °C)
Phase	3 phase
Primary Voltage	480 V delta
Power Rating	45 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Aluminium

### Ordering and shipping details

Category	US10PE216273
Discount Schedule	0PE2
GTIN	785901181309
Returnability	No
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30.00 in (76.2 cm)
Package 1 Width	20.00 in (50.8 cm)
Package 1 Length	30.00 in (76.2 cm)
Package 1 Weight	526.092 lb(US) (238.631 kg)

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No

## Contractual warranty

---

Warranty	18 months
----------	-----------

---