



Main

Range of Product	Vigirex
------------------	---------

Complementary

[Ue] rated operational voltage	130 V AC
Control Type	Manual reset
Earth-leakage protection time delay	Instantaneous
Earth-leakage sensitivity	1 A
Mounting support	DIN rail

Environment

Standards	UL 1053
-----------	---------

Ordering and shipping details

Category	US10DE200992
Discount Schedule	0DE2
GTIN	3303430563273
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Contractual warranty	
Warranty	18 months