


70S2-04-C-12-N

Solid State Relays, SPST NO, panel mounted support, blade terminal, 12A, 24 to 280V AC, 3 to 30V DC



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	12 A AC
Mounting Support	Panel mounted
Network Number of Phases	1 phase
Output Voltage	24...280 V AC

Complementary

Holding Current	50 mA
Input Current Limits	7...16 mA at 3...30 V DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Protection Type	Reverse polarity 3 V DC control
Connections Terminals	Blade terminal
Switching Voltage	1 V DC tripping
Switching Device	Triac output Zero voltage switching
Maximum Peak Voltage	600 V
Surge Current	150 A 1 cycle 48 A 60 cycles
Must Release Voltage	1 V
Voltage Drop	<1.6 V on-state AC
Thermal Resistance	2.4 °C/W
Leakage Current	6 mA at off-state
DV/dt	300 V/ms off-state at maximum rated voltage
Response Time	8.33 ms (turn-on, turn-off)
Dielectric Strength	3000 V between input and output 3000 V between terminals and chassis
Height	0.88 in (22.25 mm)
Width	1.03 in (26.2 mm)
Depth	1.23 in (31.2 mm)
Product Weight	1.66 oz (47 g)

Environment

Product Certifications	UL Recognized[RETURN]CSA[RETURN]CE
Ambient Air Temperature for Operation	-40...212 °F (-40...100 °C)
Ambient Air Temperature for Storage	-40...257 °F (-40...125 °C)

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480278556
Returnability	No
Country of origin	TW

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.10 in (2.8 cm)
Package 1 Width	1.22 in (3.1 cm)
Package 1 Length	2.28 in (5.8 cm)
Package 1 Weight	1.38 oz (39.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	5.71 in (14.5 cm)
Package 2 Width	7.99 in (20.3 cm)
Package 2 Length	10.75 in (27.3 cm)
Package 2 Weight	9.24 lb(US) (4.19 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Height	12.40 in (31.5 cm)
Package 3 Width	11.61 in (29.5 cm)
Package 3 Length	16.93 in (43.0 cm)
Package 3 Weight	38.71 lb(US) (17.56 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Wiring Diagrams

