



Main

Range of Product	Kaedra
Product or Component Type	Cable gland
Accessory / separate part category	Cabling accessory

Complementary

Cable gland type	Pg 21
Net Weight	0.06 lb(US) (0.025 kg)

Environment

Fire resistance	1562 °F (850 °C) IEC 60695-2-11
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK08 EN 62262
Ambient air temperature for operation	-13...104 °F (-25...40 °C)



Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	3303430839958
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.99 oz (28.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	175
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.88 lb(US) (5.387 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------