

# 8501XUDO1200V63

NEMA Control Relay, Type X, utility, 10A resistive at 600 VAC, 12 normally open contacts, 125 VDC coil

## Main

Range	8501X
Relay Type	Utility
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	12 NO 12 standard contact cartridges
Number of Poles	12P
Coil Voltage	125 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40...71 °C (-40...160 °F)
Electrical Connection	Screw clamp terminals
Certifications	CE[RETURN]UL Listed[RETURN]CSA
Operating Time	37 ms - pick-up 21 ms - drop-out
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	7.57 in (192.28 mm)

## Ordering and shipping details

Category	US10CP221157
Discount Schedule	0CP2
GTIN	785901743347
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.86 in (58.064 cm)
Package 1 Width	9.00 in (22.86 cm)
Package 1 Length	58.06 in (147.484 cm)
Package 1 Weight	4.050 lb(US) (1.837 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	252
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1021.918 lb(US) (463.534 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> "
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
Carbon footprint (kg CO2 eq, Total Life cycle)	270

## Contractual warranty

Warranty	18 months
----------	-----------